

Phillips Scientific

Dual NanoSecond Delay Module

CAMAC MODEL 7192

FEATURES

- * Two Independent Delay Sections
- * Total Delay of 127nSec in .5nSec Steps
- * Monotonicity is Guaranteed for Each Section
- * Both Lemo and BNC Connectors
- * Available in NIM Packaging Model 792

DESCRIPTION

The Model 7192 uses coaxial cable to provide an accurate and stable means of generating delays to 127nSec in a double width CAMAC module. Since coaxial cable is employed, no power is required and both linear or logic signals may be delayed with excellent fidelity. The configuration of two identical channels allows two signals to be delayed independently, often necessary for coincidence applications. Each channel has seven switches which select the calibrated delays of .5,1,2,4,8,16 and 32nSec. The total delay is equal to the sum of the switch settings.

GENERAL PERFORMANCE

Input and Output Characteristics:

50 ohm impedance throughout; Accepts signals to ± 350 Volts; Input and output ports are interchangeable; LEMO and BNC connectors on both ports.

Delay Controls:

Seven toggle switches per channel select .5,1,2,4,8,16 and 32nSec. The delay equals the sum of the switch settings.

Delay Range:

Selectable from 0 to 63.5nSec in .5nSec steps; 127nSec with both channels cascaded.

Delay Accuracy:

Better than ± 50 pSec or $\pm .5\%$, whichever is greater, for each delay switch inserted.

Insertion Delay:

1.9nSec, ± 100 pSec per section, with all switches in the OUT position.

Risetime and Falltime:

$t_r = t_f \leq .7$ nSec + (20pSec X delay setting), from 10% to 90%.

Maximum VSWR:

1.02 : 1 to 100MHz
1.05 : 1 to 250MHz
1.10 : 1 to 500MHz

Maximum Attenuation:


Loss db $\leq (.1$ db X # of switches IN) + (.03 db X delay setting) @ 100MHz.

Operating Temperature:

-20 °C to +85 °C ambient.

Packaging:

Standard double width CAMAC module in accordance with ESONE Report EUR-4100.



Phillips Scientific

"A THEORY DEVELOPMENT COMPANY"

150 Hilltop Road * Ramsey, NJ 07446 * (201) 934-8015 * Fax (201) 934-8269

9/96